

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208525

Luminaire Tested: **LD4B50D010TE EU4B30508035 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508035 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3501.9 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208525

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208525

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208525

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	608.6	17.4
10°-20°	1141.7	32.6
20°-30°	1024.3	29.3
30°-40°	587.8	16.8
40°-50°	117.3	3.3
50°-60°	14.8	0.4
60°-70°	6.7	0.2
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2774.6	79.2
0°-40°	3362.4	96.0
0°-60°	3494.5	99.8
0°-90°	3501.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3501.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7442	
5°	6844	609
15°	4099	1142
25°	2213	1024
35°	931	588
45°	127	117
55°	18	15
65°	6	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208525

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7442.5
2.5°	7291.3
5°	6843.9
7.5°	6191.0
10°	5477.6
12.5°	4776.2
15°	4099.1
17.5°	3506.6
20°	2998.8
22.5°	2575.5
25°	2212.8
27.5°	1922.6
30°	1602.2
32.5°	1275.7
35°	931.1
37.5°	634.8
40°	393.0
42.5°	235.8
45°	127.0
47.5°	54.4
50°	24.2
52.5°	18.1
55°	18.1
57.5°	12.1
60°	12.1
62.5°	6.0
65°	6.0
67.5°	6.0
70°	6.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)