

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207183

Luminaire Tested: **LD4B40D010 EU4B30509027 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207183  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509027 4LBMH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2524.7 lumens  
Efficiency: N/A  
Efficacy: 60.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207183

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207183

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207183

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.4	9.1
10°-20°	604.3	23.9
20°-30°	776.7	30.8
30°-40°	584.4	23.1
40°-50°	234.7	9.3
50°-60°	66.7	2.6
60°-70°	21.1	0.8
70°-80°	6.0	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1611.4	63.8
0°-40°	2195.7	87.0
0°-60°	2497.1	98.9
0°-90°	2524.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2524.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2504	
5°	2458	230
15°	2157	604
25°	1715	777
35°	937	584
45°	290	235
55°	69	67
65°	19	21
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P207183

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2503.5
2.5°	2488.3
5°	2457.8
7.5°	2400.6
10°	2328.2
12.5°	2240.6
15°	2156.8
17.5°	2061.5
20°	1958.6
22.5°	1848.1
25°	1714.7
27.5°	1554.7
30°	1368.0
32.5°	1158.4
35°	937.4
37.5°	731.6
40°	548.7
42.5°	403.9
45°	289.6
47.5°	198.1
50°	137.2
52.5°	95.3
55°	68.6
57.5°	49.5
60°	38.1
62.5°	26.7
65°	19.1
67.5°	15.2
70°	11.4
72.5°	7.6
75°	3.8
77.5°	3.8
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)