

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206160

Luminaire Tested: **LD4B50D010TE EU4B30508035 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508035 4LB5MW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5461.6 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206160

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206160

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206160

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	3.8
10°-20°	594.3	10.9
20°-30°	895.1	16.4
30°-40°	1065.1	19.5
40°-50°	1063.1	19.5
50°-60°	864.6	15.8
60°-70°	531.9	9.7
70°-80°	206.1	3.8
80°-90°	33.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1697.9	31.1
0°-40°	2763.0	50.6
0°-60°	4690.7	85.9
0°-90°	5461.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5461.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2200	
5°	2194	208
15°	2110	594
25°	1948	895
35°	1705	1065
45°	1382	1063
55°	968	865
65°	534	532
75°	188	206
85°	26	33
90°	0	



TEST NUMBER: P206160

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2200.5
2.5°	2203.7
5°	2194.0
7.5°	2181.1
10°	2164.9
12.5°	2135.8
15°	2109.9
17.5°	2071.1
20°	2029.0
22.5°	1990.2
25°	1948.1
27.5°	1889.8
30°	1831.6
32.5°	1776.6
35°	1705.4
37.5°	1627.7
40°	1556.5
42.5°	1469.2
45°	1381.8
47.5°	1287.9
50°	1187.6
52.5°	1084.1
55°	967.6
57.5°	854.3
60°	744.3
62.5°	637.5
65°	533.9
67.5°	436.9
70°	346.3
72.5°	262.1
75°	187.7
77.5°	123.0
80°	74.4
82.5°	45.3
85°	25.9
87.5°	12.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)