

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208209

Luminaire Tested: **LD4B40D010 EU4B30509027 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509027 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3149.3 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208209
CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208209

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208209

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	449.5	14.3
10°-20°	1005.0	31.9
20°-30°	999.2	31.7
30°-40°	544.1	17.3
40°-50°	125.7	4.0
50°-60°	17.7	0.6
60°-70°	6.6	0.2
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2453.7	77.9
0°-40°	2997.8	95.2
0°-60°	3141.2	99.7
0°-90°	3149.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3149.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4965	
5°	4862	450
15°	3627	1005
25°	2191	999
35°	842	544
45°	145	126
55°	19	18
65°	8	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208209

CATALOG NUMBER: LD4B40D010 EU4B30509027 4LBMLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4964.8
2.5°	4953.3
5°	4861.9
7.5°	4675.2
10°	4416.1
12.5°	4035.1
15°	3627.4
17.5°	3223.5
20°	2827.2
22.5°	2503.3
25°	2190.9
27.5°	1893.7
30°	1558.4
32.5°	1185.0
35°	842.1
37.5°	567.7
40°	369.6
42.5°	232.4
45°	144.8
47.5°	83.8
50°	41.9
52.5°	22.9
55°	19.1
57.5°	11.4
60°	11.4
62.5°	7.6
65°	7.6
67.5°	3.8
70°	3.8
72.5°	3.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)