

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206476

Luminaire Tested: **LD4B50D010TE EU4B30509035 4LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206476  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509035 4LBCSMB1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4400.7 lumens  
Efficiency: N/A  
Efficacy: 74.9 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206476

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P206476

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88				88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75				75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56				56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49				49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43				43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39				39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35				35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31				31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28				28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206476

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.8	4.0
10°-20°	500.7	11.4
20°-30°	752.7	17.1
30°-40°	893.1	20.3
40°-50°	883.9	20.1
50°-60°	694.2	15.8
60°-70°	389.3	8.8
70°-80°	109.3	2.5
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.2	32.5
0°-40°	2322.4	52.8
0°-60°	3900.5	88.6
0°-90°	4400.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4400.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1858	
5°	1855	176
15°	1776	501
25°	1634	753
35°	1432	893
45°	1152	884
55°	782	694
65°	388	389
75°	95	109
85°	0	2
90°	0	



TEST NUMBER: P206476

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1858.2
2.5°	1851.9
5°	1855.1
7.5°	1839.3
10°	1820.4
12.5°	1798.3
15°	1776.2
17.5°	1747.8
20°	1709.9
22.5°	1672.1
25°	1634.2
27.5°	1593.2
30°	1539.6
32.5°	1486.0
35°	1432.3
37.5°	1369.2
40°	1296.7
42.5°	1227.3
45°	1151.5
47.5°	1066.4
50°	978.0
52.5°	877.1
55°	782.4
57.5°	675.1
60°	574.2
62.5°	482.7
65°	388.1
67.5°	306.0
70°	227.2
72.5°	154.6
75°	94.6
77.5°	47.3
80°	12.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)