

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207095

Luminaire Tested: **LD4B50D010TE EU4B30509035 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207095  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509035 4LBWMW1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3933.5 lumens  
Efficiency: N/A  
Efficacy: 66.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207095

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207095

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207095

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.8	5.7
10°-20°	625.8	15.9
20°-30°	884.5	22.5
30°-40°	856.7	21.8
40°-50°	578.1	14.7
50°-60°	358.8	9.1
60°-70°	239.8	6.1
70°-80°	131.2	3.3
80°-90°	34.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1734.1	44.1
0°-40°	2590.9	65.9
0°-60°	3527.8	89.7
0°-90°	3933.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3933.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2384	
5°	2363	224
15°	2220	626
25°	1940	884
35°	1378	857
45°	740	578
55°	393	359
65°	240	240
75°	122	131
85°	31	35
90°	0	



TEST NUMBER: P207095

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2383.6
2.5°	2383.6
5°	2363.2
7.5°	2337.7
10°	2307.0
12.5°	2276.4
15°	2220.3
17.5°	2174.3
20°	2097.8
22.5°	2021.2
25°	1939.6
27.5°	1827.3
30°	1704.8
32.5°	1546.5
35°	1378.1
37.5°	1209.7
40°	1041.2
42.5°	872.8
45°	740.1
47.5°	617.6
50°	525.7
52.5°	449.2
55°	393.0
57.5°	347.1
60°	311.3
62.5°	275.6
65°	239.9
67.5°	209.3
70°	178.6
72.5°	153.1
75°	122.5
77.5°	97.0
80°	71.5
82.5°	51.0
85°	30.6
87.5°	10.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)