

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206776

Luminaire Tested: **LD4B40D010 EU4B30509727 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509727 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2532.9 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206776

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206776

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | | 92 |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 88 | 85 | 84 | | | | 84 |
| 3 | 100 | 93 | 87 | 82 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | 86 | 82 | 79 | 84 | 80 | 78 | 76 | | | | 76 |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 75 | 72 | 78 | 74 | 71 | 69 | | | | 69 |
| 5 | 88 | 79 | 72 | 67 | 86 | 78 | 71 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 65 | 63 | | | | 63 |
| 6 | 83 | 73 | 66 | 61 | 81 | 72 | 65 | 61 | 70 | 64 | 60 | 69 | 64 | 60 | 67 | 63 | 59 | 58 | | | | 58 |
| 7 | 78 | 67 | 60 | 56 | 76 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 | | | | 53 |
| 8 | 73 | 62 | 56 | 51 | 72 | 62 | 55 | 51 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 49 | | | | 49 |
| 9 | 69 | 58 | 51 | 47 | 68 | 58 | 51 | 47 | 57 | 51 | 47 | 56 | 50 | 47 | 55 | 50 | 46 | 45 | | | | 45 |
| 10 | 65 | 54 | 48 | 43 | 64 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | | 41 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206776

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBWWH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 153.4 | 6.1 |
| 10°-20° | 474.7 | 18.7 |
| 20°-30° | 730.2 | 28.8 |
| 30°-40° | 704.5 | 27.8 |
| 40°-50° | 367.3 | 14.5 |
| 50°-60° | 77.3 | 3.1 |
| 60°-70° | 18.0 | 0.7 |
| 70°-80° | 6.9 | 0.3 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1358.3 | 53.6 |
| 0°-40° | 2062.8 | 81.4 |
| 0°-60° | 2507.5 | 99.0 |
| 0°-90° | 2532.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2532.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1584 | |
| 5° | 1597 | 153 |
| 15° | 1680 | 475 |
| 25° | 1600 | 730 |
| 35° | 1143 | 705 |
| 45° | 467 | 367 |
| 55° | 70 | 77 |
| 65° | 17 | 18 |
| 75° | 7 | 7 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P206776

CATALOG NUMBER: LD4B40D010 EU4B30509727 4LBWWH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1583.7 |
| 2.5° | 1587.0 |
| 5° | 1596.9 |
| 7.5° | 1610.2 |
| 10° | 1630.1 |
| 12.5° | 1656.6 |
| 15° | 1679.8 |
| 17.5° | 1693.0 |
| 20° | 1683.1 |
| 22.5° | 1663.2 |
| 25° | 1600.2 |
| 27.5° | 1524.0 |
| 30° | 1424.7 |
| 32.5° | 1292.1 |
| 35° | 1143.0 |
| 37.5° | 980.7 |
| 40° | 811.7 |
| 42.5° | 642.8 |
| 45° | 467.2 |
| 47.5° | 314.7 |
| 50° | 202.1 |
| 52.5° | 122.6 |
| 55° | 69.6 |
| 57.5° | 43.1 |
| 60° | 29.8 |
| 62.5° | 23.2 |
| 65° | 16.6 |
| 67.5° | 13.3 |
| 70° | 9.9 |
| 72.5° | 9.9 |
| 75° | 6.6 |
| 77.5° | 3.3 |
| 80° | 3.3 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)