

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206786

Luminaire Tested: **LD4B50D010TE EU4B30509035 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509035 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3907.9 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206786

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206786

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92															
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84				84															
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76															
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69															
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63															
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58															
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53															
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49															
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45															
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41															

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206786

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.7	6.1
10°-20°	732.4	18.7
20°-30°	1126.6	28.8
30°-40°	1087.0	27.8
40°-50°	566.7	14.5
50°-60°	119.3	3.1
60°-70°	27.7	0.7
70°-80°	10.7	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2095.7	53.6
0°-40°	3182.7	81.4
0°-60°	3868.8	99.0
0°-90°	3907.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3907.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2443	
5°	2464	237
15°	2592	732
25°	2469	1127
35°	1764	1087
45°	721	567
55°	107	119
65°	26	28
75°	10	11
85°	0	1
90°	0	



TEST NUMBER: P206786

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2443.4
2.5°	2448.6
5°	2463.9
7.5°	2484.3
10°	2515.0
12.5°	2555.9
15°	2591.7
17.5°	2612.1
20°	2596.8
22.5°	2566.1
25°	2469.0
27.5°	2351.4
30°	2198.1
32.5°	1993.6
35°	1763.6
37.5°	1513.1
40°	1252.4
42.5°	991.7
45°	720.8
47.5°	485.6
50°	311.8
52.5°	189.1
55°	107.3
57.5°	66.5
60°	46.0
62.5°	35.8
65°	25.6
67.5°	20.4
70°	15.3
72.5°	15.3
75°	10.2
77.5°	5.1
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)