

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208408

Luminaire Tested: **LD4B40D010 EU4B30508030 4LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508030 4LBSLI1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4186.4 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208408

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208408

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	90	90	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80	80	80	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71	71	71	71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	63	63	63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57	57	57	57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51	51	51	51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	46	46	46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42	42	42	42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36	36	36	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208408

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	6.5
10°-20°	691.3	16.5
20°-30°	895.8	21.4
30°-40°	877.7	21.0
40°-50°	743.9	17.8
50°-60°	487.7	11.6
60°-70°	196.0	4.7
70°-80°	22.4	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1858.1	44.4
0°-40°	2735.8	65.3
0°-60°	3967.4	94.8
0°-90°	4186.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4186.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2989	
5°	2910	271
15°	2466	691
25°	1956	896
35°	1395	878
45°	969	744
55°	542	488
65°	190	196
75°	9	22
85°	0	1
90°	0	



TEST NUMBER: P208408

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBSL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	2989.3
2.5°	2966.1
5°	2910.5
7.5°	2817.8
10°	2701.9
12.5°	2576.8
15°	2465.6
17.5°	2345.1
20°	2224.6
22.5°	2094.8
25°	1955.8
27.5°	1812.1
30°	1663.8
32.5°	1524.8
35°	1395.0
37.5°	1288.4
40°	1172.5
42.5°	1070.6
45°	968.6
47.5°	862.0
50°	755.4
52.5°	648.8
55°	542.2
57.5°	444.9
60°	352.2
62.5°	268.8
65°	190.0
67.5°	125.1
70°	74.2
72.5°	32.4
75°	9.3
77.5°	4.6
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)