

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207399

Luminaire Tested: **LD4B50D010TE EU4B30508040 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508040 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2907.6 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207399

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207399

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207399

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.0	9.5
10°-20°	717.3	24.7
20°-30°	920.0	31.6
30°-40°	665.0	22.9
40°-50°	238.4	8.2
50°-60°	64.4	2.2
60°-70°	21.0	0.7
70°-80°	6.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1912.4	65.8
0°-40°	2577.4	88.6
0°-60°	2880.2	99.1
0°-90°	2907.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2907.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2989	
5°	2934	275
15°	2555	717
25°	2030	920
35°	1064	665
45°	287	238
55°	67	64
65°	18	21
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P207399

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2989.3
2.5°	2977.0
5°	2934.3
7.5°	2867.0
10°	2775.3
12.5°	2671.4
15°	2555.2
17.5°	2439.1
20°	2323.0
22.5°	2188.5
25°	2029.5
27.5°	1846.1
30°	1613.8
32.5°	1344.9
35°	1063.7
37.5°	806.9
40°	586.9
42.5°	415.7
45°	287.3
47.5°	195.6
50°	128.4
52.5°	91.7
55°	67.2
57.5°	48.9
60°	36.7
62.5°	30.6
65°	18.3
67.5°	12.2
70°	12.2
72.5°	6.1
75°	6.1
77.5°	6.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)