

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207193

Luminaire Tested: **LD4B50D010TE EU4B30508040 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207193  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30508040 4LBMH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4049.9 lumens  
Efficiency: N/A  
Efficacy: 68.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207193

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207193

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207193

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.5	9.1
10°-20°	969.4	23.9
20°-30°	1245.9	30.8
30°-40°	937.4	23.1
40°-50°	376.4	9.3
50°-60°	107.0	2.6
60°-70°	33.9	0.8
70°-80°	9.6	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2584.8	63.8
0°-40°	3522.2	87.0
0°-60°	4005.6	98.9
0°-90°	4049.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4049.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4016	
5°	3942	370
15°	3460	969
25°	2751	1246
35°	1504	937
45°	464	376
55°	110	107
65°	31	34
75°	6	10
85°	0	1
90°	0	



TEST NUMBER: P207193

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4015.9
2.5°	3991.4
5°	3942.5
7.5°	3850.8
10°	3734.7
12.5°	3594.1
15°	3459.6
17.5°	3306.8
20°	3141.8
22.5°	2964.5
25°	2750.6
27.5°	2493.9
30°	2194.4
32.5°	1858.2
35°	1503.7
37.5°	1173.6
40°	880.2
42.5°	647.9
45°	464.5
47.5°	317.8
50°	220.0
52.5°	152.8
55°	110.0
57.5°	79.5
60°	61.1
62.5°	42.8
65°	30.6
67.5°	24.4
70°	18.3
72.5°	12.2
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)