

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206766

Luminaire Tested: **LD4B40D010 EU4B30508030 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508030 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3546.7 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206766

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206766

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84				84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58				58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53				53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49				49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206766

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.9	6.1
10°-20°	664.7	18.7
20°-30°	1022.4	28.8
30°-40°	986.5	27.8
40°-50°	514.3	14.5
50°-60°	108.3	3.1
60°-70°	25.2	0.7
70°-80°	9.7	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.0	53.6
0°-40°	2888.5	81.4
0°-60°	3511.1	99.0
0°-90°	3546.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3546.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2218	
5°	2236	215
15°	2352	665
25°	2241	1022
35°	1600	987
45°	654	514
55°	97	108
65°	23	25
75°	9	10
85°	0	1
90°	0	



TEST NUMBER: P206766

CATALOG NUMBER: LD4B40D010 EU4B30508030 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2217.5
2.5°	2222.2
5°	2236.1
7.5°	2254.7
10°	2282.5
12.5°	2319.6
15°	2352.1
17.5°	2370.6
20°	2356.7
22.5°	2328.9
25°	2240.7
27.5°	2134.0
30°	1994.9
32.5°	1809.3
35°	1600.5
37.5°	1373.2
40°	1136.6
42.5°	900.0
45°	654.1
47.5°	440.7
50°	283.0
52.5°	171.7
55°	97.4
57.5°	60.3
60°	41.8
62.5°	32.5
65°	23.2
67.5°	18.6
70°	13.9
72.5°	13.9
75°	9.3
77.5°	4.6
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)