

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208219

Luminaire Tested: **LD4B50D010TE EU4B30508040 4LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30508040 4LBML1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5051.7 lumens  
Efficiency: N/A  
Efficacy: 86.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208219

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208219

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208219

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	721.1	14.3
10°-20°	1612.1	31.9
20°-30°	1602.7	31.7
30°-40°	872.8	17.3
40°-50°	201.7	4.0
50°-60°	28.4	0.6
60°-70°	10.5	0.2
70°-80°	2.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3935.9	77.9
0°-40°	4808.7	95.2
0°-60°	5038.8	99.7
0°-90°	5051.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5051.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7964	
5°	7799	721
15°	5819	1612
25°	3514	1603
35°	1351	873
45°	232	202
55°	31	28
65°	12	11
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P208219

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBML1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7963.9
2.5°	7945.6
5°	7798.9
7.5°	7499.4
10°	7083.8
12.5°	6472.6
15°	5818.6
17.5°	5170.7
20°	4535.1
22.5°	4015.6
25°	3514.4
27.5°	3037.6
30°	2499.8
32.5°	1900.8
35°	1350.7
37.5°	910.7
40°	592.9
42.5°	372.8
45°	232.3
47.5°	134.5
50°	67.2
52.5°	36.7
55°	30.6
57.5°	18.3
60°	18.3
62.5°	12.2
65°	12.2
67.5°	6.1
70°	6.1
72.5°	6.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)