

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205641

Luminaire Tested: **LD4B50D010TE EU4B30508040 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205641  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30508040 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5362.4 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205641

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205641

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205641

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	314.1	5.9
10°-20°	832.4	15.5
20°-30°	1118.0	20.8
30°-40°	1144.4	21.3
40°-50°	990.5	18.5
50°-60°	658.8	12.3
60°-70°	270.6	5.0
70°-80°	32.2	0.6
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2264.6	42.2
0°-40°	3408.9	63.6
0°-60°	5058.3	94.3
0°-90°	5362.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5362.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3399	
5°	3346	314
15°	2973	832
25°	2439	1118
35°	1828	1144
45°	1290	991
55°	731	659
65°	267	271
75°	14	32
85°	0	1
90°	0	



TEST NUMBER: P205641

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3398.7
2.5°	3391.7
5°	3346.0
7.5°	3275.7
10°	3180.8
12.5°	3075.4
15°	2973.4
17.5°	2843.4
20°	2716.9
22.5°	2583.3
25°	2439.2
27.5°	2284.6
30°	2129.9
32.5°	1975.3
35°	1827.6
37.5°	1687.1
40°	1553.5
42.5°	1419.9
45°	1289.9
47.5°	1152.8
50°	1012.2
52.5°	871.6
55°	731.1
57.5°	608.0
60°	481.5
62.5°	365.5
65°	267.1
67.5°	175.7
70°	101.9
72.5°	49.2
75°	14.1
77.5°	7.0
80°	3.5
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)