

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207390

Luminaire Tested: **LD4B40D010 EU4B30509030 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207390  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509030 4LBMGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1884.7 lumens  
Efficiency: N/A  
Efficacy: 45.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207390

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207390

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207390

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.3	9.5
10°-20°	464.9	24.7
20°-30°	596.3	31.6
30°-40°	431.0	22.9
40°-50°	154.5	8.2
50°-60°	41.7	2.2
60°-70°	13.6	0.7
70°-80°	4.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1239.6	65.8
0°-40°	1670.6	88.6
0°-60°	1866.8	99.1
0°-90°	1884.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1884.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1938	
5°	1902	178
15°	1656	465
25°	1316	596
35°	689	431
45°	186	155
55°	44	42
65°	12	14
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P207390

CATALOG NUMBER: LD4B40D010 EU4B30509030 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1937.6
2.5°	1929.7
5°	1901.9
7.5°	1858.3
10°	1798.9
12.5°	1731.5
15°	1656.3
17.5°	1581.0
20°	1505.7
22.5°	1418.5
25°	1315.5
27.5°	1196.6
30°	1046.1
32.5°	871.7
35°	689.4
37.5°	523.0
40°	380.4
42.5°	269.4
45°	186.2
47.5°	126.8
50°	83.2
52.5°	59.4
55°	43.6
57.5°	31.7
60°	23.8
62.5°	19.8
65°	11.9
67.5°	7.9
70°	7.9
72.5°	4.0
75°	4.0
77.5°	4.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)