

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207302

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509040 4LBMWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3464.2 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207302

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P207302

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207302

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.1	11.0
10°-20°	977.2	28.2
20°-30°	1146.5	33.1
30°-40°	725.5	20.9
40°-50°	194.3	5.6
50°-60°	27.2	0.8
60°-70°	10.1	0.3
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2503.8	72.3
0°-40°	3229.3	93.2
0°-60°	3450.8	99.6
0°-90°	3464.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3464.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4114	
5°	4048	380
15°	3500	977
25°	2533	1146
35°	1151	726
45°	220	194
55°	26	27
65°	10	10
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P207302

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4114.3
2.5°	4098.9
5°	4047.8
7.5°	3965.9
10°	3848.2
12.5°	3694.7
15°	3500.2
17.5°	3300.7
20°	3060.1
22.5°	2814.5
25°	2533.1
27.5°	2226.0
30°	1883.2
32.5°	1509.6
35°	1151.4
37.5°	834.1
40°	573.1
42.5°	368.4
45°	220.0
47.5°	122.8
50°	66.5
52.5°	35.8
55°	25.6
57.5°	20.5
60°	15.4
62.5°	15.4
65°	10.2
67.5°	5.1
70°	5.1
72.5°	5.1
75°	5.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)