

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207817

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBNGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207817  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509040 4LBNGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2113.3 lumens  
Efficiency: N/A  
Efficacy: 36.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207817

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207817

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 97  | 96  | 95  | 94  |    |    |   |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 92  | 91  | 89  | 87  |    |    |   |
| 3   | 103 | 96  | 91  | 87  | 101 | 95  | 90  | 87  | 92  | 88  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 81  |    |    |   |
| 4   | 97  | 90  | 84  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  |    |    |   |
| 5   | 93  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 70  |    |    |   |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 69  | 77  | 72  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 66  |    |    |   |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 62  |    |    |   |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 59  | 66  | 62  | 59  | 58  |    |    |   |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 54  |    |    |   |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 52  | 51  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207817

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNGPH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 230.4  | 10.9      |
| 10°-20°   | 577.6  | 27.3      |
| 20°-30°   | 703.9  | 33.3      |
| 30°-40°   | 464.4  | 22.0      |
| 40°-50°   | 106.9  | 5.1       |
| 50°-60°   | 20.5   | 1.0       |
| 60°-70°   | 7.5    | 0.4       |
| 70°-80°   | 2.0    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1512.0 | 71.5      |
| 0°-40°    | 1976.4 | 93.5      |
| 0°-60°    | 2103.8 | 99.5      |
| 0°-90°    | 2113.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2113.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2534 |      |
| 5°  | 2473 | 230  |
| 15° | 2068 | 578  |
| 25° | 1546 | 704  |
| 35° | 742  | 464  |
| 45° | 118  | 107  |
| 55° | 20   | 20   |
| 65° | 5    | 8    |
| 75° | 0    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P207817

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNGPH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2534.3 |
| 2.5°  | 2529.2 |
| 5°    | 2472.9 |
| 7.5°  | 2396.1 |
| 10°   | 2293.7 |
| 12.5° | 2191.3 |
| 15°   | 2068.4 |
| 17.5° | 1940.4 |
| 20°   | 1807.3 |
| 22.5° | 1689.6 |
| 25°   | 1546.2 |
| 27.5° | 1402.8 |
| 30°   | 1218.5 |
| 32.5° | 993.3  |
| 35°   | 742.4  |
| 37.5° | 517.1  |
| 40°   | 332.8  |
| 42.5° | 204.8  |
| 45°   | 117.8  |
| 47.5° | 61.4   |
| 50°   | 35.8   |
| 52.5° | 30.7   |
| 55°   | 20.5   |
| 57.5° | 15.4   |
| 60°   | 15.4   |
| 62.5° | 10.2   |
| 65°   | 5.1    |
| 67.5° | 5.1    |
| 70°   | 5.1    |
| 72.5° | 5.1    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)