

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206674

Luminaire Tested: **LD4B40D010 EU4B30509730 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509730 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2550.7 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206674

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206674

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206674

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.6	6.1
10°-20°	451.1	17.7
20°-30°	665.7	26.1
30°-40°	656.9	25.8
40°-50°	402.0	15.8
50°-60°	154.1	6.0
60°-70°	48.2	1.9
70°-80°	14.1	0.6
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1273.4	49.9
0°-40°	1930.4	75.7
0°-60°	2486.5	97.5
0°-90°	2550.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2550.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1644	
5°	1644	157
15°	1599	451
25°	1457	666
35°	1066	657
45°	516	402
55°	163	154
65°	45	48
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P206674

CATALOG NUMBER: LD4B40D010 EU4B30509730 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1644.0
2.5°	1647.5
5°	1644.0
7.5°	1640.6
10°	1630.2
12.5°	1616.4
15°	1599.1
17.5°	1578.3
20°	1547.1
22.5°	1512.5
25°	1457.1
27.5°	1387.9
30°	1301.4
32.5°	1194.1
35°	1066.0
37.5°	924.1
40°	778.8
42.5°	643.8
45°	515.7
47.5°	401.5
50°	304.6
52.5°	225.0
55°	162.7
57.5°	114.2
60°	83.1
62.5°	62.3
65°	45.0
67.5°	34.6
70°	24.2
72.5°	17.3
75°	13.8
77.5°	6.9
80°	6.9
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)