

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208532

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509040 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2962.7 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208532

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208532

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208532

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	514.9	17.4
10°-20°	965.9	32.6
20°-30°	866.6	29.3
30°-40°	497.3	16.8
40°-50°	99.2	3.3
50°-60°	12.5	0.4
60°-70°	5.7	0.2
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2347.4	79.2
0°-40°	2844.7	96.0
0°-60°	2956.4	99.8
0°-90°	2962.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2962.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6297	
5°	5790	515
15°	3468	966
25°	1872	867
35°	788	497
45°	107	99
55°	15	13
65°	5	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208532

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6296.6
2.5°	6168.7
5°	5790.2
7.5°	5237.8
10°	4634.2
12.5°	4040.9
15°	3468.0
17.5°	2966.7
20°	2537.0
22.5°	2179.0
25°	1872.1
27.5°	1626.6
30°	1355.5
32.5°	1079.3
35°	787.7
37.5°	537.1
40°	332.5
42.5°	199.5
45°	107.4
47.5°	46.0
50°	20.5
52.5°	15.3
55°	15.3
57.5°	10.2
60°	10.2
62.5°	5.1
65°	5.1
67.5°	5.1
70°	5.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)