

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208512

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508035 4LBNWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2750.8 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208512

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P208512

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208512

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.0	17.4
10°-20°	896.8	32.6
20°-30°	804.6	29.3
30°-40°	461.7	16.8
40°-50°	92.1	3.3
50°-60°	11.6	0.4
60°-70°	5.2	0.2
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2179.5	79.2
0°-40°	2641.2	96.0
0°-60°	2744.9	99.8
0°-90°	2750.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2750.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5846	
5°	5376	478
15°	3220	897
25°	1738	805
35°	731	462
45°	100	92
55°	14	12
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208512

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5846.2
2.5°	5727.4
5°	5376.0
7.5°	4863.1
10°	4302.7
12.5°	3751.8
15°	3219.9
17.5°	2754.5
20°	2355.6
22.5°	2023.1
25°	1738.2
27.5°	1510.2
30°	1258.5
32.5°	1002.1
35°	731.4
37.5°	498.7
40°	308.7
42.5°	185.2
45°	99.7
47.5°	42.7
50°	19.0
52.5°	14.2
55°	14.2
57.5°	9.5
60°	9.5
62.5°	4.7
65°	4.7
67.5°	4.7
70°	4.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)