

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206251

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206251  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508035 4LBPSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4466.0 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206251

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206251

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206251

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.5	3.8
10°-20°	486.0	10.9
20°-30°	731.9	16.4
30°-40°	870.9	19.5
40°-50°	869.3	19.5
50°-60°	707.0	15.8
60°-70°	434.9	9.7
70°-80°	168.5	3.8
80°-90°	27.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.4	31.1
0°-40°	2259.3	50.6
0°-60°	3835.6	85.9
0°-90°	4466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4466.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1799	
5°	1794	170
15°	1725	486
25°	1593	732
35°	1394	871
45°	1130	869
55°	791	707
65°	437	435
75°	154	168
85°	21	27
90°	0	



TEST NUMBER: P206251

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1799.4
2.5°	1802.0
5°	1794.1
7.5°	1783.5
10°	1770.3
12.5°	1746.5
15°	1725.3
17.5°	1693.5
20°	1659.1
22.5°	1627.4
25°	1593.0
27.5°	1545.4
30°	1497.7
32.5°	1452.7
35°	1394.5
37.5°	1331.0
40°	1272.8
42.5°	1201.4
45°	1129.9
47.5°	1053.2
50°	971.1
52.5°	886.5
55°	791.2
57.5°	698.6
60°	608.6
62.5°	521.3
65°	436.6
67.5°	357.2
70°	283.1
72.5°	214.3
75°	153.5
77.5°	100.6
80°	60.9
82.5°	37.0
85°	21.2
87.5°	10.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)