

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206043

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206043  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508035 4LBSB1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3616.0 lumens  
Efficiency: N/A  
Efficacy: 86.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206043

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P206043

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76	76	76	76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65	65	65	65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50	50	50	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44	44	44	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39	39	39	39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35	35	35	35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32	32	32	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29	29	29	29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206043

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.6	4.2
10°-20°	427.2	11.8
20°-30°	635.4	17.6
30°-40°	739.4	20.4
40°-50°	720.7	19.9
50°-60°	554.4	15.3
60°-70°	306.5	8.5
70°-80°	81.2	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1213.2	33.5
0°-40°	1952.6	54.0
0°-60°	3227.7	89.3
0°-90°	3616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3616.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1595	
5°	1586	151
15°	1513	427
25°	1380	635
35°	1187	739
45°	935	721
55°	619	554
65°	307	306
75°	69	81
85°	0	1
90°	0	



TEST NUMBER: P206043

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1595.1
2.5°	1595.1
5°	1585.9
7.5°	1572.2
10°	1563.0
12.5°	1535.5
15°	1512.6
17.5°	1489.7
20°	1457.6
22.5°	1425.5
25°	1379.7
27.5°	1333.8
30°	1288.0
32.5°	1237.6
35°	1187.2
37.5°	1123.0
40°	1068.0
42.5°	1008.4
45°	935.1
47.5°	866.3
50°	788.4
52.5°	705.9
55°	618.8
57.5°	536.3
60°	458.4
62.5°	380.4
65°	307.1
67.5°	238.4
70°	174.2
72.5°	119.2
75°	68.8
77.5°	32.1
80°	4.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)