

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205627

Luminaire Tested: **LD4B40D010 EU4B30508035 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508035 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4170.8 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205627

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205627

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205627

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.3	5.9
10°-20°	647.4	15.5
20°-30°	869.5	20.8
30°-40°	890.1	21.3
40°-50°	770.4	18.5
50°-60°	512.4	12.3
60°-70°	210.5	5.0
70°-80°	25.0	0.6
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1761.3	42.2
0°-40°	2651.4	63.6
0°-60°	3934.2	94.3
0°-90°	4170.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4170.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2643	
5°	2602	244
15°	2313	647
25°	1897	870
35°	1422	890
45°	1003	770
55°	569	512
65°	208	210
75°	11	25
85°	0	1
90°	0	



TEST NUMBER: P205627

CATALOG NUMBER: LD4B40D010 EU4B30508035 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2643.4
2.5°	2637.9
5°	2602.4
7.5°	2547.7
10°	2473.9
12.5°	2391.9
15°	2312.6
17.5°	2211.5
20°	2113.1
22.5°	2009.2
25°	1897.1
27.5°	1776.9
30°	1656.6
32.5°	1536.3
35°	1421.5
37.5°	1312.1
40°	1208.3
42.5°	1104.4
45°	1003.2
47.5°	896.6
50°	787.3
52.5°	677.9
55°	568.6
57.5°	472.9
60°	374.5
62.5°	284.3
65°	207.8
67.5°	136.7
70°	79.3
72.5°	38.3
75°	10.9
77.5°	5.5
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)