

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208119

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBWL11**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508050 4LBWL1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5329.7 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208119

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208119

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54																
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208119

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.3	6.0
10°-20°	1007.8	18.9
20°-30°	1572.2	29.5
30°-40°	1529.7	28.7
40°-50°	764.1	14.3
50°-60°	118.3	2.2
60°-70°	14.3	0.3
70°-80°	4.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2899.3	54.4
0°-40°	4429.1	83.1
0°-60°	5311.4	99.7
0°-90°	5329.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5329.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3266	
5°	3308	319
15°	3559	1008
25°	3455	1572
35°	2484	1530
45°	958	764
55°	98	118
65°	12	14
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P208119

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3265.6
2.5°	3277.8
5°	3308.4
7.5°	3357.2
10°	3418.2
12.5°	3497.6
15°	3558.6
17.5°	3607.4
20°	3613.6
22.5°	3570.8
25°	3454.8
27.5°	3283.9
30°	3070.3
32.5°	2801.7
35°	2484.3
37.5°	2136.4
40°	1770.2
42.5°	1379.5
45°	958.3
47.5°	616.5
50°	372.3
52.5°	201.4
55°	97.7
57.5°	42.7
60°	24.4
62.5°	18.3
65°	12.2
67.5°	12.2
70°	6.1
72.5°	6.1
75°	6.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)