

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206463

Luminaire Tested: **LD4B40D010 EU4B30509035 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509035 4LBCSMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3459.7 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206463

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206463

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206463

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	4.0
10°-20°	393.7	11.4
20°-30°	591.8	17.1
30°-40°	702.1	20.3
40°-50°	694.8	20.1
50°-60°	545.8	15.8
60°-70°	306.0	8.8
70°-80°	85.9	2.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1123.6	32.5
0°-40°	1825.8	52.8
0°-60°	3066.4	88.6
0°-90°	3459.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3459.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1461	
5°	1458	138
15°	1396	394
25°	1285	592
35°	1126	702
45°	905	695
55°	615	546
65°	305	306
75°	74	86
85°	0	1
90°	0	



TEST NUMBER: P206463

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1460.9
2.5°	1455.9
5°	1458.4
7.5°	1446.0
10°	1431.1
12.5°	1413.8
15°	1396.4
17.5°	1374.1
20°	1344.3
22.5°	1314.5
25°	1284.8
27.5°	1252.5
30°	1210.4
32.5°	1168.2
35°	1126.0
37.5°	1076.4
40°	1019.4
42.5°	964.8
45°	905.3
47.5°	838.3
50°	768.9
52.5°	689.5
55°	615.1
57.5°	530.8
60°	451.4
62.5°	379.5
65°	305.1
67.5°	240.6
70°	178.6
72.5°	121.5
75°	74.4
77.5°	37.2
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)