

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208226

Luminaire Tested: **LD4B50D010TE EU4B30509050 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509050 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4250.2 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208226

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P208226

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 109 | 104 | 100 | 97 | 107 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 3 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 89 | 94 | 90 | 87 | 91 | 88 | 86 | 89 | 87 | 85 | 83 | | | | | | | | | | | | | | | | | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 82 | 89 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 78 | | | | | | | | | | | | | | | | | | | |
| 5 | 94 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 79 | 76 | 82 | 78 | 75 | 81 | 77 | 75 | 73 | | | | | | | | | | | | | | | | | | | |
| 6 | 90 | 82 | 76 | 72 | 89 | 81 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 69 | | | | | | | | | | | | | | | | | | | |
| 7 | 86 | 77 | 72 | 68 | 85 | 77 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 8 | 82 | 73 | 68 | 64 | 81 | 73 | 67 | 64 | 72 | 67 | 64 | 71 | 66 | 63 | 70 | 66 | 63 | 62 | | | | | | | | | | | | | | | | | | | |
| 9 | 79 | 70 | 64 | 60 | 78 | 69 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 60 | 67 | 63 | 60 | 58 | | | | | | | | | | | | | | | | | | | |
| 10 | 75 | 66 | 61 | 57 | 74 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 64 | 60 | 57 | 56 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208226

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBMLI1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 606.7 | 14.3 |
| 10°-20° | 1356.3 | 31.9 |
| 20°-30° | 1348.5 | 31.7 |
| 30°-40° | 734.3 | 17.3 |
| 40°-50° | 169.7 | 4.0 |
| 50°-60° | 23.9 | 0.6 |
| 60°-70° | 8.9 | 0.2 |
| 70°-80° | 2.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3311.4 | 77.9 |
| 0°-40° | 4045.8 | 95.2 |
| 0°-60° | 4239.4 | 99.7 |
| 0°-90° | 4250.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4250.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6700 | |
| 5° | 6562 | 607 |
| 15° | 4896 | 1356 |
| 25° | 2957 | 1348 |
| 35° | 1136 | 734 |
| 45° | 195 | 170 |
| 55° | 26 | 24 |
| 65° | 10 | 9 |
| 75° | 0 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P208226

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBMLI1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 6700.4 |
| 2.5° | 6685.0 |
| 5° | 6561.6 |
| 7.5° | 6309.6 |
| 10° | 5959.9 |
| 12.5° | 5445.7 |
| 15° | 4895.5 |
| 17.5° | 4350.4 |
| 20° | 3815.6 |
| 22.5° | 3378.5 |
| 25° | 2956.8 |
| 27.5° | 2555.7 |
| 30° | 2103.2 |
| 32.5° | 1599.3 |
| 35° | 1136.4 |
| 37.5° | 766.2 |
| 40° | 498.8 |
| 42.5° | 313.7 |
| 45° | 195.4 |
| 47.5° | 113.1 |
| 50° | 56.6 |
| 52.5° | 30.9 |
| 55° | 25.7 |
| 57.5° | 15.4 |
| 60° | 15.4 |
| 62.5° | 10.3 |
| 65° | 10.3 |
| 67.5° | 5.1 |
| 70° | 5.1 |
| 72.5° | 5.1 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)