

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207185

Luminaire Tested: **LD4B40D010 EU4B30509035 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509035 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2662.7 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207185

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207185

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207185

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.0	9.1
10°-20°	637.4	23.9
20°-30°	819.1	30.8
30°-40°	616.3	23.1
40°-50°	247.5	9.3
50°-60°	70.3	2.6
60°-70°	22.3	0.8
70°-80°	6.3	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1699.4	63.8
0°-40°	2315.7	87.0
0°-60°	2633.5	98.9
0°-90°	2662.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2662.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2640	
5°	2592	243
15°	2275	637
25°	1808	819
35°	989	616
45°	305	248
55°	72	70
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P207185

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2640.3
2.5°	2624.2
5°	2592.1
7.5°	2531.8
10°	2455.4
12.5°	2363.0
15°	2274.6
17.5°	2174.1
20°	2065.6
22.5°	1949.1
25°	1808.4
27.5°	1639.6
30°	1442.7
32.5°	1221.7
35°	988.6
37.5°	771.6
40°	578.7
42.5°	426.0
45°	305.4
47.5°	209.0
50°	144.7
52.5°	100.5
55°	72.3
57.5°	52.2
60°	40.2
62.5°	28.1
65°	20.1
67.5°	16.1
70°	12.1
72.5°	8.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)