

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206670

Luminaire Tested: **LD4B40D010 EU4B30509035 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509035 4LBWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2959.9 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206670  
CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206670

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206670

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.7	6.1
10°-20°	523.5	17.7
20°-30°	772.5	26.1
30°-40°	762.4	25.8
40°-50°	466.5	15.8
50°-60°	178.9	6.0
60°-70°	55.9	1.9
70°-80°	16.4	0.6
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1477.7	49.9
0°-40°	2240.1	75.7
0°-60°	2885.5	97.5
0°-90°	2959.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2959.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1908	
5°	1908	182
15°	1856	524
25°	1691	773
35°	1237	762
45°	598	467
55°	189	179
65°	52	56
75°	16	16
85°	0	2
90°	0	



TEST NUMBER: P206670

CATALOG NUMBER: LD4B40D010 EU4B30509035 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1907.8
2.5°	1911.8
5°	1907.8
7.5°	1903.8
10°	1891.7
12.5°	1875.7
15°	1855.6
17.5°	1831.5
20°	1795.3
22.5°	1755.2
25°	1690.9
27.5°	1610.6
30°	1510.2
32.5°	1385.7
35°	1237.1
37.5°	1072.4
40°	903.7
42.5°	747.1
45°	598.4
47.5°	465.9
50°	353.4
52.5°	261.1
55°	188.8
57.5°	132.5
60°	96.4
62.5°	72.3
65°	52.2
67.5°	40.2
70°	28.1
72.5°	20.1
75°	16.1
77.5°	8.0
80°	8.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)