

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206356

Luminaire Tested: **LD4B40D010 EU4B30508040 4LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206356  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508040 4LBCSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4417.9 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206356

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206356

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206356

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.0	3.9
10°-20°	486.7	11.0
20°-30°	732.2	16.6
30°-40°	867.7	19.6
40°-50°	863.5	19.5
50°-60°	696.1	15.8
60°-70°	421.1	9.5
70°-80°	156.3	3.5
80°-90°	23.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1389.8	31.5
0°-40°	2257.6	51.1
0°-60°	3817.2	86.4
0°-90°	4417.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4417.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1804	
5°	1796	171
15°	1724	487
25°	1590	732
35°	1390	868
45°	1124	864
55°	776	696
65°	423	421
75°	142	156
85°	19	23
90°	0	



TEST NUMBER: P206356

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1804.4
2.5°	1804.4
5°	1796.4
7.5°	1791.0
10°	1775.0
12.5°	1748.2
15°	1724.1
17.5°	1697.3
20°	1665.2
22.5°	1633.1
25°	1590.3
27.5°	1544.7
30°	1493.9
32.5°	1445.7
35°	1389.5
37.5°	1330.6
40°	1261.0
42.5°	1194.0
45°	1124.4
47.5°	1046.8
50°	961.1
52.5°	872.8
55°	776.4
57.5°	690.7
60°	594.3
62.5°	508.7
65°	423.0
67.5°	342.7
70°	267.7
72.5°	200.8
75°	141.9
77.5°	91.0
80°	53.5
82.5°	32.1
85°	18.7
87.5°	8.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)