

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208513

Luminaire Tested: **LD4B40D010 EU4B30508040 4LBNWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208513  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508040 4LBNWH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2780.5 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208513

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBNWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P208513

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBNWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208513

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBNWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	483.2	17.4
10°-20°	906.5	32.6
20°-30°	813.3	29.3
30°-40°	466.7	16.8
40°-50°	93.1	3.3
50°-60°	11.8	0.4
60°-70°	5.3	0.2
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2203.0	79.2
0°-40°	2669.7	96.0
0°-60°	2774.6	99.8
0°-90°	2780.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2780.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5909	
5°	5434	483
15°	3255	906
25°	1757	813
35°	739	467
45°	101	93
55°	14	12
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208513

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBNWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5909.3
2.5°	5789.3
5°	5434.1
7.5°	4915.6
10°	4349.2
12.5°	3792.3
15°	3254.7
17.5°	2784.2
20°	2381.0
22.5°	2045.0
25°	1757.0
27.5°	1526.5
30°	1272.1
32.5°	1012.9
35°	739.3
37.5°	504.0
40°	312.0
42.5°	187.2
45°	100.8
47.5°	43.2
50°	19.2
52.5°	14.4
55°	14.4
57.5°	9.6
60°	9.6
62.5°	4.8
65°	4.8
67.5°	4.8
70°	4.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)