

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P295270

Luminaire Tested: **LD4B30DE010 EU4B30509030D2W 4LBW0LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P295270  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35289)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30DE010 EU4B30509030D2W 4LBW0LI  
Description: PORTFOLIO 4" D2W RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH  
Light Source: D2W 1800K-3000K CCT TUNING RANGE  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2387.7 lumens  
Efficiency: N/A  
Efficacy: 78.3 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P295270

CATALOG NUMBER: LD4B30DE010 EU4B30509030D2W 4LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P295270

CATALOG NUMBER: LD4B30DE010 EU4B30509030D2W 4LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	159848
5°	162554
10°	169892
15°	180328
20°	188223
25°	186596
30°	173538
35°	148455
40°	113105
45°	66335
50°	28353
55°	8343
60°	2382
65°	1422
70°	863
75°	1140
80°	0
85°	0



TEST NUMBER: P295270

CATALOG NUMBER: LD4B30DE010 EU4B30509030D2W 4LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.1	6.0
10°-20°	451.5	18.9
20°-30°	704.3	29.5
30°-40°	685.3	28.7
40°-50°	342.3	14.3
50°-60°	53.0	2.2
60°-70°	6.4	0.3
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.9	54.4
0°-40°	1984.2	83.1
0°-60°	2379.5	99.7
0°-90°	2387.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2387.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1463	
5°	1482	143
15°	1594	451
25°	1548	704
35°	1113	685
45°	429	342
55°	44	53
65°	6	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P295270

CATALOG NUMBER: LD4B30DE010 EU4B30509030D2W 4LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1463.0
2.5°	1468.4
5°	1482.1
7.5°	1504.0
10°	1531.3
12.5°	1566.9
15°	1594.2
17.5°	1616.1
20°	1618.8
22.5°	1599.7
25°	1547.8
27.5°	1471.2
30°	1375.5
32.5°	1255.2
35°	1113.0
37.5°	957.1
40°	793.0
42.5°	618.0
45°	429.3
47.5°	276.2
50°	166.8
52.5°	90.2
55°	43.8
57.5°	19.1
60°	10.9
62.5°	8.2
65°	5.5
67.5°	5.5
70°	2.7
72.5°	2.7
75°	2.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)