

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206665

Luminaire Tested: **LD4B40D010 EU4B30508040 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508040 4LBWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3539.3 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206665

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206665

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206665

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.2	6.1
10°-20°	626.0	17.7
20°-30°	923.7	26.1
30°-40°	911.6	25.8
40°-50°	557.9	15.8
50°-60°	213.9	6.0
60°-70°	66.8	1.9
70°-80°	19.6	0.6
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1767.0	49.9
0°-40°	2678.6	75.7
0°-60°	3450.3	97.5
0°-90°	3539.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3539.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2281	
5°	2281	217
15°	2219	626
25°	2022	924
35°	1479	912
45°	716	558
55°	226	214
65°	62	67
75°	19	20
85°	0	3
90°	0	



TEST NUMBER: P206665

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2281.3
2.5°	2286.1
5°	2281.3
7.5°	2276.5
10°	2262.1
12.5°	2242.8
15°	2218.8
17.5°	2190.0
20°	2146.8
22.5°	2098.8
25°	2021.9
27.5°	1925.9
30°	1805.8
32.5°	1656.9
35°	1479.2
37.5°	1282.3
40°	1080.6
42.5°	893.3
45°	715.6
47.5°	557.1
50°	422.6
52.5°	312.2
55°	225.7
57.5°	158.5
60°	115.3
62.5°	86.4
65°	62.4
67.5°	48.0
70°	33.6
72.5°	24.0
75°	19.2
77.5°	9.6
80°	9.6
82.5°	4.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)