

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206768

Luminaire Tested: **LD4B40D010 EU4B30508040 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508040 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3673.7 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206768

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206768

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206768

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.6	6.1
10°-20°	688.5	18.7
20°-30°	1059.1	28.8
30°-40°	1021.9	27.8
40°-50°	532.8	14.5
50°-60°	112.2	3.1
60°-70°	26.0	0.7
70°-80°	10.1	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1970.2	53.6
0°-40°	2992.0	81.4
0°-60°	3636.9	99.0
0°-90°	3673.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3673.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2297	
5°	2316	223
15°	2436	689
25°	2321	1059
35°	1658	1022
45°	678	533
55°	101	112
65°	24	26
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P206768

CATALOG NUMBER: LD4B40D010 EU4B30508040 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2297.0
2.5°	2301.8
5°	2316.2
7.5°	2335.5
10°	2364.3
12.5°	2402.7
15°	2436.4
17.5°	2455.6
20°	2441.2
22.5°	2412.4
25°	2321.0
27.5°	2210.5
30°	2066.4
32.5°	1874.1
35°	1657.9
37.5°	1422.4
40°	1177.3
42.5°	932.3
45°	677.6
47.5°	456.5
50°	293.1
52.5°	177.8
55°	100.9
57.5°	62.5
60°	43.2
62.5°	33.6
65°	24.0
67.5°	19.2
70°	14.4
72.5°	14.4
75°	9.6
77.5°	4.8
80°	4.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)