

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207289

Luminaire Tested: **LD4B40D010 EU4B30509040 4LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207289  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30509040 4LBMWH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2723.5 lumens  
Efficiency: N/A  
Efficacy: 65.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207289

CATALOG NUMBER: LD4B40D010 EU4B30509040 4LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207289

CATALOG NUMBER: LD4B40D010 EU4B30509040 4LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66		
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62		
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207289

CATALOG NUMBER: LD4B40D010 EU4B30509040 4LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.8	11.0
10°-20°	768.3	28.2
20°-30°	901.3	33.1
30°-40°	570.4	20.9
40°-50°	152.8	5.6
50°-60°	21.4	0.8
60°-70°	7.9	0.3
70°-80°	2.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1968.4	72.3
0°-40°	2538.8	93.2
0°-60°	2713.0	99.6
0°-90°	2723.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2723.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3234	
5°	3182	299
15°	2752	768
25°	1991	901
35°	905	570
45°	173	153
55°	20	21
65°	8	8
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P207289

CATALOG NUMBER: LD4B40D010 EU4B30509040 4LBMWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3234.5
2.5°	3222.5
5°	3182.2
7.5°	3117.9
10°	3025.3
12.5°	2904.7
15°	2751.8
17.5°	2594.9
20°	2405.8
22.5°	2212.7
25°	1991.4
27.5°	1750.0
30°	1480.5
32.5°	1186.8
35°	905.2
37.5°	655.8
40°	450.6
42.5°	289.7
45°	173.0
47.5°	96.6
50°	52.3
52.5°	28.2
55°	20.1
57.5°	16.1
60°	12.1
62.5°	12.1
65°	8.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	4.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)