

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206563

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206563  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B40D010 EU4B30508050 4LBCSMMS1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W  
DL3-44.71W DLE-39.33W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3730.8 lumens  
Efficiency: N/A  
Efficacy: 89.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206563

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P206563

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206563

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.5	4.3
10°-20°	453.0	12.1
20°-30°	661.7	17.7
30°-40°	756.9	20.3
40°-50°	727.4	19.5
50°-60°	561.7	15.1
60°-70°	313.5	8.4
70°-80°	91.2	2.4
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.2	34.2
0°-40°	2033.1	54.5
0°-60°	3322.2	89.0
0°-90°	3730.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1713	
5°	1699	161
15°	1607	453
25°	1438	662
35°	1211	757
45°	948	727
55°	630	562
65°	314	313
75°	80	91
85°	2	4
90°	0	



TEST NUMBER: P206563

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1713.3
2.5°	1713.3
5°	1698.8
7.5°	1691.6
10°	1667.4
12.5°	1638.5
15°	1607.1
17.5°	1575.7
20°	1529.9
22.5°	1493.7
25°	1438.2
27.5°	1382.7
30°	1327.2
32.5°	1271.7
35°	1211.4
37.5°	1151.0
40°	1081.1
42.5°	1018.3
45°	948.3
47.5°	868.7
50°	793.9
52.5°	711.9
55°	629.8
57.5°	545.4
60°	465.7
62.5°	386.1
65°	313.7
67.5°	246.1
70°	183.4
72.5°	127.9
75°	79.6
77.5°	41.0
80°	14.5
82.5°	4.8
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)