

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207593

Luminaire Tested: **LD4B40D010 EU4B30508050 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30508050 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3311.8 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207593

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207593

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89																			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80																			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71																			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64																			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53																			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49																			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45																			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207593

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.0	7.0
10°-20°	624.7	18.9
20°-30°	830.7	25.1
30°-40°	679.4	20.5
40°-50°	395.7	11.9
50°-60°	262.4	7.9
60°-70°	172.6	5.2
70°-80°	91.1	2.8
80°-90°	22.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1688.4	51.0
0°-40°	2367.8	71.5
0°-60°	3025.9	91.4
0°-90°	3311.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3311.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2514	
5°	2485	233
15°	2226	625
25°	1823	831
35°	1084	679
45°	499	396
55°	293	262
65°	173	173
75°	86	91
85°	19	22
90°	0	



TEST NUMBER: P207593

CATALOG NUMBER: LD4B40D010 EU4B30508050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2514.0
2.5°	2509.2
5°	2485.3
7.5°	2427.7
10°	2365.3
12.5°	2307.7
15°	2226.2
17.5°	2135.0
20°	2058.2
22.5°	1952.7
25°	1823.2
27.5°	1684.0
30°	1506.5
32.5°	1295.4
35°	1084.3
37.5°	892.4
40°	724.5
42.5°	594.9
45°	499.0
47.5°	422.2
50°	369.4
52.5°	326.2
55°	292.7
57.5°	259.1
60°	225.5
62.5°	201.5
65°	172.7
67.5°	148.7
70°	124.7
72.5°	105.6
75°	86.4
77.5°	67.2
80°	48.0
82.5°	33.6
85°	19.2
87.5°	4.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)