

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274264

Luminaire Tested: **LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1808-906-1)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 950.0 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274264

CATALOG NUMBER: LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P274264

CATALOG NUMBER: LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76		
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	73	71		
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67		
7	84	75	69	65	83	74	69	65	73	68	65	72	67	64	71	67	64	62		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141263
5°	136385
10°	124326
15°	110129
20°	95623
25°	80917
30°	64003
35°	40335
40°	20753
45°	9163
50°	3604
55°	2153
60°	1246
65°	724
70°	447
75°	591
80°	0
85°	0



TEST NUMBER: P274264

CATALOG NUMBER: LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	12.1
10°-20°	271.4	28.6
20°-30°	305.9	32.2
30°-40°	191.6	20.2
40°-50°	51.2	5.4
50°-60°	10.8	1.1
60°-70°	3.3	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.1	72.9
0°-40°	883.7	93.0
0°-60°	945.8	99.6
0°-90°	950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1293	
5°	1244	115
15°	974	271
25°	671	306
35°	302	192
45°	59	51
55°	11	11
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274264

CATALOG NUMBER: LD4B20DE010W2N2050 EU4B1020W2N902050 4LBN0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1292.9
2.5°	1281.6
5°	1243.5
7.5°	1187.0
10°	1120.6
12.5°	1047.1
15°	973.6
17.5°	898.7
20°	822.4
22.5°	746.1
25°	671.2
27.5°	597.7
30°	507.3
32.5°	405.5
35°	302.4
37.5°	214.8
40°	145.5
42.5°	94.7
45°	59.3
47.5°	33.9
50°	21.2
52.5°	15.5
55°	11.3
57.5°	8.5
60°	5.7
62.5°	4.2
65°	2.8
67.5°	2.8
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)