

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206051

Luminaire Tested: **LD4B40D010 EU4B30509050 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206051
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B40D010 EU4B30509050 4LBSB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-43.02W DE010-42.54W D5LT-42.539W DMX-41.87W DL2-41.57W
DL3-44.71W DLE-39.33W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3075.1 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206051

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P206051

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76																
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65																
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50																
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44																
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39																
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35																
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32																
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206051

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	4.2
10°-20°	363.3	11.8
20°-30°	540.4	17.6
30°-40°	628.8	20.4
40°-50°	612.9	19.9
50°-60°	471.4	15.3
60°-70°	260.6	8.5
70°-80°	69.0	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.7	33.6
0°-40°	1660.6	54.0
0°-60°	2745.0	89.3
0°-90°	3075.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3075.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1356	
5°	1349	128
15°	1286	363
25°	1173	540
35°	1010	629
45°	795	613
55°	526	471
65°	261	261
75°	58	69
85°	0	1
90°	0	



TEST NUMBER: P206051

CATALOG NUMBER: LD4B40D010 EU4B30509050 4LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1356.5
2.5°	1356.5
5°	1348.8
7.5°	1337.1
10°	1329.3
12.5°	1305.9
15°	1286.4
17.5°	1266.9
20°	1239.6
22.5°	1212.3
25°	1173.3
27.5°	1134.4
30°	1095.4
32.5°	1052.5
35°	1009.6
37.5°	955.0
40°	908.3
42.5°	857.6
45°	795.2
47.5°	736.7
50°	670.5
52.5°	600.3
55°	526.2
57.5°	456.1
60°	389.8
62.5°	323.5
65°	261.2
67.5°	202.7
70°	148.1
72.5°	101.4
75°	58.5
77.5°	27.3
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)