

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208322

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509024 4LBNLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2765.7 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208322

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208322

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90																																				
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																																				
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81																																				
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77																																				
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73																																				
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69																																				
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																																				
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63																																				
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208322

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	560.9	20.3
10°-20°	960.2	34.7
20°-30°	763.2	27.6
30°-40°	404.0	14.6
40°-50°	69.6	2.5
50°-60°	5.2	0.2
60°-70°	2.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2284.3	82.6
0°-40°	2688.2	97.2
0°-60°	2763.0	99.9
0°-90°	2765.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2765.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7117	
5°	6380	561
15°	3471	960
25°	1644	763
35°	639	404
45°	72	70
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208322

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBNI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7117.2
2.5°	6934.0
5°	6380.3
7.5°	5656.3
10°	4889.6
12.5°	4148.5
15°	3471.3
17.5°	2840.9
20°	2338.3
22.5°	1955.0
25°	1644.1
27.5°	1392.8
30°	1141.5
32.5°	885.9
35°	638.9
37.5°	421.7
40°	251.3
42.5°	144.8
45°	72.4
47.5°	25.6
50°	8.5
52.5°	8.5
55°	4.3
57.5°	4.3
60°	4.3
62.5°	4.3
65°	4.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)