

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839150

Luminaire Tested: **LD4C05D010 EU4059030 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839150  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C05D010 EU4059030 4LBSH  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 642.0 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839150

CATALOG NUMBER: LD4C05D010 EU4059030 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839150

CATALOG NUMBER: LD4C05D010 EU4059030 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41254
5°	41054
10°	40207
15°	38754
20°	36960
25°	34973
30°	32996
35°	31060
40°	29252
45°	27260
50°	24866
55°	21954
60°	18575
65°	14593
70°	10417
75°	5696
80°	990
85°	0



TEST NUMBER: P839150

CATALOG NUMBER: LD4C05D010 EU4059030 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.4	4.9
10°-20°	85.5	13.3
20°-30°	118.7	18.5
30°-40°	129.5	20.2
40°-50°	120.8	18.8
50°-60°	91.7	14.3
60°-70°	50.2	7.8
70°-80°	13.8	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.6	36.7
0°-40°	365.2	56.9
0°-60°	577.8	90.0
0°-90°	642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	336	
5°	333	31
15°	305	85
25°	258	119
35°	207	130
45°	157	121
55°	102	92
65°	50	50
75°	12	14
85°	0	0
90°	0	



TEST NUMBER: P839150

CATALOG NUMBER: LD4C05D010 EU4059030 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	335.8
2.5°	335.8
5°	332.9
7.5°	328.7
10°	322.3
12.5°	313.9
15°	304.7
17.5°	293.4
20°	282.7
22.5°	270.0
25°	258.0
27.5°	246.0
30°	232.6
32.5°	219.8
35°	207.1
37.5°	194.4
40°	182.4
42.5°	169.6
45°	156.9
47.5°	144.2
50°	130.1
52.5°	116.6
55°	102.5
57.5°	89.1
60°	75.6
62.5°	62.2
65°	50.2
67.5°	38.9
70°	29.0
72.5°	19.8
75°	12.0
77.5°	5.7
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)