

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206059

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509024 4LBSB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3243.3 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206059

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P206059

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65																			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206059

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.0	4.2
10°-20°	383.1	11.8
20°-30°	570.0	17.6
30°-40°	663.2	20.4
40°-50°	646.5	19.9
50°-60°	497.2	15.3
60°-70°	274.9	8.5
70°-80°	72.8	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.1	33.6
0°-40°	1751.4	54.0
0°-60°	2895.0	89.3
0°-90°	3243.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3243.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1431	
5°	1422	135
15°	1357	383
25°	1238	570
35°	1065	663
45°	839	646
55°	555	497
65°	276	275
75°	62	73
85°	0	1
90°	0	



TEST NUMBER: P206059

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1430.7
2.5°	1430.7
5°	1422.5
7.5°	1410.2
10°	1401.9
12.5°	1377.3
15°	1356.7
17.5°	1336.2
20°	1307.4
22.5°	1278.6
25°	1237.5
27.5°	1196.4
30°	1155.3
32.5°	1110.0
35°	1064.8
37.5°	1007.3
40°	957.9
42.5°	904.5
45°	838.7
47.5°	777.0
50°	707.1
52.5°	633.1
55°	555.0
57.5°	481.0
60°	411.1
62.5°	341.2
65°	275.5
67.5°	213.8
70°	156.2
72.5°	106.9
75°	61.7
77.5°	28.8
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)