

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839167

Luminaire Tested: **LD4C08D010 EU4089035 4LBPSMW**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839167
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089035 4LBPSMW
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 875.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839167

CATALOG NUMBER: LD4C08D010 EU4089035 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839167

CATALOG NUMBER: LD4C08D010 EU4089035 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50419
5°	50328
10°	50062
15°	49476
20°	48582
25°	47525
30°	46402
35°	45068
40°	43253
45°	40134
50°	34575
55°	27566
60°	21475
65°	16075
70°	11674
75°	9256
80°	8631
85°	8598



TEST NUMBER: P839167

CATALOG NUMBER: LD4C08D010 EU4089035 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	4.4
10°-20°	109.6	12.5
20°-30°	161.5	18.5
30°-40°	187.6	21.4
40°-50°	176.3	20.1
50°-60°	116.7	13.3
60°-70°	56.2	6.4
70°-80°	21.7	2.5
80°-90°	6.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.8	35.4
0°-40°	497.3	56.8
0°-60°	790.3	90.3
0°-90°	875.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	410	
5°	408	39
15°	389	110
25°	351	161
35°	300	188
45°	231	176
55°	129	117
65°	55	56
75°	20	22
85°	6	7
90°	0	



TEST NUMBER: P839167

CATALOG NUMBER: LD4C08D010 EU4089035 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	410.4
2.5°	410.0
5°	408.1
7.5°	405.4
10°	401.3
12.5°	395.7
15°	389.0
17.5°	380.9
20°	371.6
22.5°	361.4
25°	350.6
27.5°	339.1
30°	327.1
32.5°	314.3
35°	300.5
37.5°	285.5
40°	269.7
42.5°	251.9
45°	231.0
47.5°	207.2
50°	180.9
52.5°	154.2
55°	128.7
57.5°	106.9
60°	87.4
62.5°	69.9
65°	55.3
67.5°	42.9
70°	32.5
72.5°	24.7
75°	19.5
77.5°	15.8
80°	12.2
82.5°	9.1
85°	6.1
87.5°	3.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)