

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206680

Luminaire Tested: **LD4B50D010TE EU4B30509024 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509024 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3140.6 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206680

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206680

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206680

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.8	6.1
10°-20°	555.5	17.7
20°-30°	819.7	26.1
30°-40°	808.9	25.8
40°-50°	495.0	15.8
50°-60°	189.8	6.0
60°-70°	59.3	1.9
70°-80°	17.4	0.6
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1567.9	49.9
0°-40°	2376.8	75.7
0°-60°	3061.6	97.5
0°-90°	3140.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3140.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2024	
5°	2024	193
15°	1969	555
25°	1794	820
35°	1313	809
45°	635	495
55°	200	190
65°	55	59
75°	17	17
85°	0	2
90°	0	



TEST NUMBER: P206680

CATALOG NUMBER: LD4B50D010TE EU4B30509024 4LBWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2024.3
2.5°	2028.5
5°	2024.3
7.5°	2020.0
10°	2007.2
12.5°	1990.2
15°	1968.9
17.5°	1943.3
20°	1905.0
22.5°	1862.3
25°	1794.1
27.5°	1708.9
30°	1602.4
32.5°	1470.3
35°	1312.6
37.5°	1137.9
40°	958.9
42.5°	792.7
45°	635.0
47.5°	494.3
50°	375.0
52.5°	277.0
55°	200.3
57.5°	140.6
60°	102.3
62.5°	76.7
65°	55.4
67.5°	42.6
70°	29.8
72.5°	21.3
75°	17.0
77.5°	8.5
80°	8.5
82.5°	4.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)