

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839169

Luminaire Tested: **LD4C08D010 EU4089035 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089035 4LBSLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 913.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839169

CATALOG NUMBER: LD4C08D010 EU4089035 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839169

CATALOG NUMBER: LD4C08D010 EU4089035 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																											
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																											
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																											
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																											
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																											
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																											
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																											
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																											
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																											
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80088
5°	78273
10°	73502
15°	68389
20°	63421
25°	57814
30°	51481
35°	45623
40°	41008
45°	36694
50°	31478
55°	25338
60°	18870
65°	12035
70°	5819
75°	949
80°	707
85°	0



TEST NUMBER: P839169

CATALOG NUMBER: LD4C08D010 EU4089035 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	6.5
10°-20°	150.8	16.5
20°-30°	195.4	21.4
30°-40°	191.4	21.0
40°-50°	162.2	17.8
50°-60°	106.4	11.6
60°-70°	42.7	4.7
70°-80°	4.9	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.2	44.4
0°-40°	596.6	65.3
0°-60°	865.2	94.8
0°-90°	913.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	913.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	652	
5°	635	59
15°	538	151
25°	426	195
35°	304	191
45°	211	162
55°	118	106
65°	41	43
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P839169

CATALOG NUMBER: LD4C08D010 EU4089035 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	651.9
2.5°	646.9
5°	634.7
7.5°	614.5
10°	589.2
12.5°	562.0
15°	537.7
17.5°	511.4
20°	485.1
22.5°	456.9
25°	426.5
27.5°	395.2
30°	362.9
32.5°	332.5
35°	304.2
37.5°	281.0
40°	255.7
42.5°	233.5
45°	211.2
47.5°	188.0
50°	164.7
52.5°	141.5
55°	118.3
57.5°	97.0
60°	76.8
62.5°	58.6
65°	41.4
67.5°	27.3
70°	16.2
72.5°	7.1
75°	2.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)