

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839173

Luminaire Tested: **LD4C08D010 EU4089050 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089050 4LBPSMW
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 894.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839173

CATALOG NUMBER: LD4C08D010 EU4089050 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839173

CATALOG NUMBER: LD4C08D010 EU4089050 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51512
5°	51426
10°	51147
15°	50557
20°	49641
25°	48555
30°	47409
35°	46058
40°	44199
45°	41003
50°	35320
55°	28166
60°	21942
65°	16424
70°	11925
75°	9446
80°	8844
85°	8880



TEST NUMBER: P839173

CATALOG NUMBER: LD4C08D010 EU4089050 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	4.4
10°-20°	111.9	12.5
20°-30°	165.0	18.5
30°-40°	191.6	21.4
40°-50°	180.1	20.1
50°-60°	119.2	13.3
60°-70°	57.5	6.4
70°-80°	22.2	2.5
80°-90°	6.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.5	35.4
0°-40°	508.1	56.8
0°-60°	807.5	90.3
0°-90°	894.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	894.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	419	
5°	417	40
15°	398	112
25°	358	165
35°	307	192
45°	236	180
55°	132	119
65°	56	57
75°	20	22
85°	6	7
90°	0	



TEST NUMBER: P839173

CATALOG NUMBER: LD4C08D010 EU4089050 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	419.3
2.5°	418.9
5°	417.0
7.5°	414.2
10°	410.0
12.5°	404.3
15°	397.5
17.5°	389.1
20°	379.7
22.5°	369.2
25°	358.2
27.5°	346.5
30°	334.2
32.5°	321.1
35°	307.1
37.5°	291.7
40°	275.6
42.5°	257.4
45°	236.0
47.5°	211.7
50°	184.8
52.5°	157.5
55°	131.5
57.5°	109.2
60°	89.3
62.5°	71.5
65°	56.5
67.5°	43.8
70°	33.2
72.5°	25.2
75°	19.9
77.5°	16.1
80°	12.5
82.5°	9.3
85°	6.3
87.5°	3.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)