

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839197

Luminaire Tested: **LD4C10D010 EU4109035 4LBPSMW**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10D010 EU4109035 4LBPSMW
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1003.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839197

CATALOG NUMBER: LD4C10D010 EU4109035 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839197

CATALOG NUMBER: LD4C10D010 EU4109035 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57790
5°	57690
10°	57384
15°	56713
20°	55694
25°	54479
30°	53183
35°	51667
40°	49588
45°	46007
50°	39620
55°	31614
60°	24620
65°	18430
70°	13362
75°	10585
80°	9905
85°	9867



TEST NUMBER: P839197

CATALOG NUMBER: LD4C10D010 EU4109035 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	4.4
10°-20°	125.6	12.5
20°-30°	185.1	18.5
30°-40°	215.0	21.4
40°-50°	202.1	20.1
50°-60°	133.8	13.3
60°-70°	64.5	6.4
70°-80°	24.9	2.5
80°-90°	7.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.1	35.4
0°-40°	570.1	56.8
0°-60°	905.9	90.3
0°-90°	1003.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1003.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	470	
5°	468	44
15°	446	126
25°	402	185
35°	344	215
45°	265	202
55°	148	134
65°	63	64
75°	22	25
85°	7	8
90°	0	



TEST NUMBER: P839197

CATALOG NUMBER: LD4C10D010 EU4109035 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	470.4
2.5°	470.0
5°	467.8
7.5°	464.7
10°	460.0
12.5°	453.6
15°	445.9
17.5°	436.6
20°	426.0
22.5°	414.3
25°	401.9
27.5°	388.7
30°	374.9
32.5°	360.2
35°	344.5
37.5°	327.3
40°	309.2
42.5°	288.8
45°	264.8
47.5°	237.5
50°	207.3
52.5°	176.7
55°	147.6
57.5°	122.5
60°	100.2
62.5°	80.2
65°	63.4
67.5°	49.1
70°	37.2
72.5°	28.3
75°	22.3
77.5°	18.1
80°	14.0
82.5°	10.4
85°	7.0
87.5°	4.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)