

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206262

Luminaire Tested: **LD4B50D010TE EU4B30508027 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508027 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5302.8 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206262
CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206262

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206262

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.4	3.8
10°-20°	577.0	10.9
20°-30°	869.1	16.4
30°-40°	1034.1	19.5
40°-50°	1032.2	19.5
50°-60°	839.4	15.8
60°-70°	516.4	9.7
70°-80°	200.1	3.8
80°-90°	32.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.5	31.1
0°-40°	2682.6	50.6
0°-60°	4554.2	85.9
0°-90°	5302.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5302.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2136	
5°	2130	202
15°	2048	577
25°	1891	869
35°	1656	1034
45°	1342	1032
55°	939	839
65°	518	516
75°	182	200
85°	25	32
90°	0	



TEST NUMBER: P206262

CATALOG NUMBER: LD4B50D010TE EU4B30508027 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2136.5
2.5°	2139.6
5°	2130.2
7.5°	2117.7
10°	2101.9
12.5°	2073.7
15°	2048.5
17.5°	2010.8
20°	1970.0
22.5°	1932.3
25°	1891.4
27.5°	1834.9
30°	1778.3
32.5°	1724.9
35°	1655.8
37.5°	1580.4
40°	1511.3
42.5°	1426.4
45°	1341.6
47.5°	1250.5
50°	1153.1
52.5°	1052.5
55°	939.4
57.5°	829.5
60°	722.6
62.5°	619.0
65°	518.4
67.5°	424.2
70°	336.2
72.5°	254.5
75°	182.2
77.5°	119.4
80°	72.3
82.5°	44.0
85°	25.1
87.5°	12.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)