

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839208

Luminaire Tested: **LD4C15D010 EU4159027 4LBSLI**

Issue Date: 2/9/2022

Test Information

Test Method: LM-79-08
Report Number: P839208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EU4159027 4LBSLI
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1522.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839208

CATALOG NUMBER: LD4C15D010 EU4159027 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839208

CATALOG NUMBER: LD4C15D010 EU4159027 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133517
5°	130488
10°	122541
15°	114011
20°	105741
25°	96379
30°	85810
35°	76053
40°	68367
45°	61192
50°	52483
55°	42217
60°	31450
65°	20087
70°	9662
75°	1614
80°	1203
85°	0



TEST NUMBER: P839208

CATALOG NUMBER: LD4C15D010 EU4159027 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.5	6.5
10°-20°	251.3	16.5
20°-30°	325.7	21.4
30°-40°	319.1	21.0
40°-50°	270.5	17.8
50°-60°	177.3	11.6
60°-70°	71.3	4.7
70°-80°	8.2	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.5	44.4
0°-40°	994.6	65.3
0°-60°	1442.4	94.8
0°-90°	1522.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1522.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1087	
5°	1058	99
15°	896	251
25°	711	326
35°	507	319
45°	352	270
55°	197	177
65°	69	71
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P839208

CATALOG NUMBER: LD4C15D010 EU4159027 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1086.8
2.5°	1078.3
5°	1058.1
7.5°	1024.4
10°	982.3
12.5°	936.8
15°	896.4
17.5°	852.6
20°	808.8
22.5°	761.6
25°	711.0
27.5°	658.8
30°	604.9
32.5°	554.3
35°	507.1
37.5°	468.4
40°	426.3
42.5°	389.2
45°	352.2
47.5°	313.4
50°	274.6
52.5°	235.9
55°	197.1
57.5°	161.8
60°	128.0
62.5°	97.7
65°	69.1
67.5°	45.5
70°	26.9
72.5°	11.8
75°	3.4
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)