

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839222

Luminaire Tested: **LD4C20D010 EU4209027 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P839222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20D010 EU4209027 4LBSH
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1882.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839222

CATALOG NUMBER: LD4C20D010 EU4209027 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839222

CATALOG NUMBER: LD4C20D010 EU4209027 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120925
5°	120363
10°	117875
15°	113591
20°	108369
25°	102519
30°	96705
35°	91051
40°	85736
45°	79921
50°	72876
55°	64364
60°	54473
65°	42761
70°	30532
75°	16708
80°	2971
85°	0



TEST NUMBER: P839222

CATALOG NUMBER: LD4C20D010 EU4209027 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	4.9
10°-20°	250.6	13.3
20°-30°	348.0	18.5
30°-40°	379.7	20.2
40°-50°	354.2	18.8
50°-60°	268.9	14.3
60°-70°	147.2	7.8
70°-80°	40.5	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.8	36.7
0°-40°	1070.5	56.9
0°-60°	1693.7	90.0
0°-90°	1882.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1882.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	984	
5°	976	92
15°	893	251
25°	756	348
35°	607	380
45°	460	354
55°	300	269
65°	147	147
75°	35	41
85°	0	1
90°	0	



TEST NUMBER: P839222

CATALOG NUMBER: LD4C20D010 EU4209027 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	984.3
2.5°	984.3
5°	976.0
7.5°	963.6
10°	944.9
12.5°	920.1
15°	893.1
17.5°	860.0
20°	828.9
22.5°	791.6
25°	756.3
27.5°	721.1
30°	681.7
32.5°	644.4
35°	607.1
37.5°	569.8
40°	534.6
42.5°	497.3
45°	460.0
47.5°	422.7
50°	381.3
52.5°	341.9
55°	300.5
57.5°	261.1
60°	221.7
62.5°	182.4
65°	147.1
67.5°	113.9
70°	85.0
72.5°	58.0
75°	35.2
77.5°	16.6
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)