

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839244

Luminaire Tested: **LD4C25D010 EU4259035 4LBSLI**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839244  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C25D010 EU4259035 4LBSLI  
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2599.0 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839244

CATALOG NUMBER: LD4C25D010 EU4259035 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839244

CATALOG NUMBER: LD4C25D010 EU4259035 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	227991
5°	222820
10°	209253
15°	194673
20°	180549
25°	164589
30°	146526
35°	129880
40°	116736
45°	104488
50°	89638
55°	72096
60°	53712
65°	34302
70°	16523
75°	2753
80°	2052
85°	0



TEST NUMBER: P839244

CATALOG NUMBER: LD4C25D010 EU4259035 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.3	6.5
10°-20°	429.2	16.5
20°-30°	556.1	21.4
30°-40°	544.9	21.0
40°-50°	461.9	17.8
50°-60°	302.7	11.6
60°-70°	121.7	4.7
70°-80°	13.9	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1153.5	44.4
0°-40°	1698.4	65.3
0°-60°	2463.0	94.8
0°-90°	2599.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2599.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1856	
5°	1807	168
15°	1531	429
25°	1214	556
35°	866	545
45°	601	462
55°	337	303
65°	118	122
75°	6	14
85°	0	0
90°	0	



TEST NUMBER: P839244

CATALOG NUMBER: LD4C25D010 EU4259035 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1855.8
2.5°	1841.4
5°	1806.8
7.5°	1749.3
10°	1677.4
12.5°	1599.7
15°	1530.6
17.5°	1455.9
20°	1381.0
22.5°	1300.5
25°	1214.2
27.5°	1125.0
30°	1032.9
32.5°	946.6
35°	866.0
37.5°	799.9
40°	727.9
42.5°	664.6
45°	601.4
47.5°	535.2
50°	469.0
52.5°	402.8
55°	336.6
57.5°	276.2
60°	218.6
62.5°	166.9
65°	118.0
67.5°	77.7
70°	46.0
72.5°	20.1
75°	5.8
77.5°	2.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)